

Task Light (P005193)

TECHNICAL DATA SHEET

Purpose

The Task Light supplies the caregivers with a task light for patient illumination.

Standards

As manufactured, the Task Light is compliant with the codes and standards as listed below.

For USA installations:

- National Fire Protection Association®¹
NFPA 99: *Standard For Health Care Facilities*
- NFPA 70: *National Electrical Code*® (NEC®)
- Part-18 in Title-47 of the US Code of Federal Regulations (47CFR-18)
- ANSI/UL-1598: *Luminaires*

For Canadian installations:

- Canadian Standards Association (CSA®)²
Parts - 1 and 2 of the Canadian Electrical Code (CSA 22.1 and CSA C22.2) and CSA C22.2 No. 250.0: *Luminaires*

General Description and Responsibilities

- The Task Light is a one-piece fixture with two lamps for patient task illumination. A wall switch controls the lights.
- This WittRock ceiling light is cULus-listed (IEVV for USA installations and IEVV7 for Canadian installations) under UL-File No: E318785.
- The Task Light is a prefabricated and factory wired fluorescent light fixture that is mounted and recessed into the ceiling structure of a general care area. The Task Light must be installed and positioned a minimum of 90" (229 cm) above the finished floor.

- The installation contractor is to install the Task Light and connect facility service wiring in accordance with Hill-Rom's *Task Light (P005193) and (P005194) to Wall Box—Installation Instructions* (151220), and all national, local, and state or provincial building codes, and electrical code.

Manufacturer Qualifications

- Shipment is the responsibility of WittRock.
- The Task Light is shipped in a corrugated carton and is skid-wrapped.
- The Task Light configuration options are established at the time the order is accepted.

Design Requirements

- The fixture is encased in 20-gauge CRS, one-piece seam welded construction.
- The flange and grid are 20-gauge CRS, four-piece construction that is spot-welded to the encasement.
- The corners are mitered and spot-welded.
- The encasement is finished in a white polyester powder coat finish and is processed through a 5-step pre-treated procedure.
- The light has an antimicrobial finish.
- Attached to the encasement is an inner flange of 18-gauge CRS with a black matte powder coat finish.
- A semi-circular aluminum parabolic slide louver shields the examination compartment lamps.
- A steel and pearlescent acrylic diffuser (with holes in it) shields the ambient compartment lamps.
- A clear lamp shield protects the read lamp compartment.

Lamp Requirements

- The Task Light requires two type F54T5HO (54 watt rapid start) lamps.
- The lamps are not supplied with the Task Light.

1. National Fire Protection Association®, National Electrical Code®, and NEC® are registered trademarks of National Fire Protection Association, Inc.

2. CSA® is a registered trademark of Canadian Standards Association, Inc.

Task Light (P005193)

TECHNICAL DATA SHEET

Performance Requirements

The values listed in this section are in footcandles as measured on the bed surface with the Task Light mounted in a 90" (229 cm) ceiling and with the bed in the low position.

- **TASK LIGHT ONLY**
47" (120 cm) above finished floor (AFF)
Foot: 79 Seat: 99 Head: 93

Components per Light

- One Model P005193 Task Light

Electrical System

- 18 AWG wire is the minimum wire dimension used in the Task Light circuitry.
- The ballast is Class P, rapid start, sound rated A, high power factor in the specified voltage. All ballast are 47CFR-18 compliant.

Installation and Maintenance

- The Task Light is designed to be mounted in 1" (2.54 cm) wide, 24" (61 cm) x 48" (122 cm) T-grid ceiling tracks.
- All hardware and wire required to mount the Task Light is supplied by the contractor.
- The Task Light must be installed and positioned a minimum of 90" (229 cm) above the finished floor and in accordance with Hill-Rom's *Task Light (P005193) and (P005194) to Wall Box—Installation Instructions* (151220), and all national, local, and state or provincial building codes, and electrical code.
- Supply connections are to be made to one circuit.

Service

A list of service parts for the Task Light is available in Hill-Rom's *Recessed Mounted Luminaires Service Manual* (154190).

Submittals

- The Task Light will not be assembled until all approvals are received.
- WittRock will supply physical samples only if specifically asked, and the cost to do so is negotiated.

Warranty

WittRock warrants all materials and workmanship to be of the quality, quantity, and character specified or shown. Defects because of the use of incorrect workmanship or material, found or made known to WittRock within one (1) year of delivery, will be made good by WittRock at no added expense to the owner.

Order Data

Order part number P005193 for the Task Light.

Dimensions

Table 1. Dimensions

Dimension	Value
Length	47" (120 cm)
Width	8" (20 cm)
Depth	3" (8 cm)
Weight	21 lbs. (10 kg)—with lamps
	20 lbs. (9 kg)—without lamps


Electric Power Connection Options

The electric power connection for the Task Light is as follows (see figure 1 on page 3):

Task Light (P005193)

TECHNICAL DATA SHEET

Figure 1. Task Light Electric Power Connection



TASK LIGHT
P005193

152729_1_001

Task Light (P005193)

TECHNICAL DATA SHEET



8829 STATE ROUTE 46 E
GREENSBURG, IN 47240 USA
Customer Service: 812.222.0373
Technical Support: 812.222.0373

International: Contact your distributor.
www.WittRockhc.com

CSA® is a registered trademark of Canadian Standards Association, Inc.

WittRock® is a registered trademark of WittRock, Inc.

National Electrical Code® is a registered trademark of National Fire Protection Association, Inc.

National Fire Protection Association® is a registered trademark of National Fire Protection Association, Inc.

NEC® is a registered trademark of National Fire Protection Association, Inc.

WittRock, Inc. (WittRock) reserves the right to make changes without notice in design, specifications, and models. The only warranty WittRock makes is the express written warranty extended on the sale or rental of its products.

© 2008 by WittRock, Inc. ALL RIGHTS RESERVED.

No part of this text shall be reproduced without written permission from WittRock, Inc.